



LF1001008014

REACH
 RoHS

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 10 mm

Length 2000 mm

Trunking width 12 mm

Distance bottom-punch along trunking-direction 125 mm

Cover, door

Lid shape premounted

Materials

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Internal/useful cross section 84 mm²

Equipment

Compartment quantity 1

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK06

Use conditions

Operating temperature -5...60 °C