



LF1001008014



## Technical properties

### Configuration

Antibacterial treatment	No
-------------------------	----

### Connectivity

Trunking coupling	without coupler
-------------------	-----------------

### Dimensions

Trunking height	10 mm
-----------------	-------

Length	2000 mm
--------	---------

Trunking width	12 mm
----------------	-------

Distance bottom-punch along trunking-direction	125 mm
--	--------

### Cover, door

Lid shape	premounted
-----------	------------

### Materials

Colour	brown
--------	-------

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

Transparent	No
-------------	----

### Cable

Internal/useful cross section	84 mm <sup>2</sup>
-------------------------------	--------------------

### Equipment

Compartment quantity	1
----------------------	---

### Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

### Safety

Protection index IP	IP30
---------------------	------

### Use conditions

Operating temperature	-5...60 °C
-----------------------	------------