



LF1501508014

Trunking from PVC LF 15x15mm brown

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 15 mm

Length 2000 mm

Trunking width 15 mm

Distance bottom-punch along trunking-direction 125 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 1

Maximum number of cables (Ø 11 mm, 50% fill) 1

Cover, door

Lid shape premounted

Materials

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Internal/useful cross section 150 mm²

Equipment

Compartment quantity 1

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK06

Use conditions

Operating temperature

-5...60 °C

temperatur

Ambient temperature

-5...65 °C