



LF1501508014

**Trunking from PVC LF 15x15mm brown**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 15 mm

Length 2000 mm

Trunking width 15 mm

Distance bottom-punch along trunking-direction 125 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 1

Maximum number of cables (Ø 11 mm, 50% fill) 1

**Cover, door**

Lid shape premounted

**Materials**

Material group plastic

Type of surface treatment untreated

Transparent No

**Cable**

Internal/useful cross section 150 mm<sup>2</sup>

**Equipment**

Compartment quantity 1

**Standards**

Approvals EN50085-2-1

European directive RoHS voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK06

**Use conditions**

---

Operating temperature

-5...60 °C

**temperatur**

---

Ambient temperature

-5...65 °C