



LF300M

Cylindrical fuse-links for industrial applications 10x38mm aM 0,5A 500V AC 120kA

Technical properties

Functions

Release characteristic fuses	Time-lag
------------------------------	----------

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	120 kA
--	--------

Rated operational voltage U_e	500 V
---------------------------------	-------

Type of supply voltage	AC
------------------------	----

Electric current

Rated current	0.5 A
---------------	-------

Rated ultimate short-circuit breaking capacity I_{cu} AC IEC 60947-2	120 kA
--	--------

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under I_N	0.49 W
------------------------------	--------

Standards

European directive WEEE	concerned
-------------------------	-----------