



LF301M

Cylindrical fuse-links for industrial applications 10x38mm aM 1A 500V AC 120kA

Technical properties

Functions

Release characteristic fuses Time-lag

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1 120 kA

Rated operational voltage U_e 500 V

Type of supply voltage AC

Electric current

Rated current 1 A

Rated ultimate short-circuit breaking capacity I_{cu} AC IEC 60947-2 120 kA

Frequency

Frequency 50 to 60 Hz

Power

Total power loss under I_N 0.1 W

Standards

European directive WEEE concerned