



LF301PV

PV Fuse-link 10x38 mm 1000V DC 1A

Technical properties

Functions

Release characteristic fuses	Super fast (FF)
------------------------------	-----------------

Main electrical features

Rated short circuit breaking capacity Icn AC according IEC60898-1	30 kA
Rated operational voltage Ue	0 / 1000 V
Type of supply voltage	DC

Electric current

Rated current	1 A
Rated ultimate short-circuit breaking capacity Icu AC IEC 60947-2	30 kA

Fuse

CharactFuse	gPV
Fuse Size	10.3 x 38

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	0.76 W
---------------------------	--------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes