



LF302PV

**PV Fuse-link 10x38 mm 1000V DC 2A**

**Technical properties**

**Functions**

Release characteristic fuses	Super fast (FF)
------------------------------	-----------------

**Main electrical features**

Rated short circuit breaking capacity Icn AC according IEC60898-1	30 kA
Rated operational voltage Ue	0 / 1000 V
Type of supply voltage	DC

**Voltage**

Rated operational voltage in DC	1000 V
---------------------------------	--------

**Electric current**

Rated current	2 A
Rated ultimate short-circuit breaking capacity Icu AC IEC 60947-2	30 kA

**Fuse**

CharactFuse	gPV
Fuse Size	10.3 x 38

**Frequency**

Frequency	50 to 60 Hz
-----------	-------------

**Power**

Total power loss under IN	1.54 W
---------------------------	--------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes