



LF303PV



PV Fuse-link 10x38 mm 1000V DC 3A

Technical properties

Functions

Release characteristic fuses Super fast (FF)

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1 30 kA

Rated operational voltage U_e 0 / 1000 V

Voltage

Rated operational voltage in DC 900 V

Electric current

Rated current 3 A

Power

Total power loss under I_N 1.2 W

Use conditions

Operating temperature -25...70 °C