



LF303PV



**PV Fuse-link 10x38 mm 1000V DC 3A**

**Technical properties**

**Functions**

Release characteristic fuses	Super fast (FF)
------------------------------	-----------------

**Main electrical features**

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	30 kA
Rated operational voltage $U_e$	0 / 1000 V

**Voltage**

Rated operational voltage in DC	900 V
---------------------------------	-------

**Electric current**

Rated current	3 A
---------------	-----

**Power**

Total power loss under $I_N$	1.2 W
------------------------------	-------

**Use conditions**

Operating temperature	-25...70 °C
-----------------------	-------------