



LF303PV



PV Fuse-link 10x38 mm 1000V DC 3A

Technical properties

Functions

Release characteristic fuses	Super fast (FF)
------------------------------	-----------------

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	30 kA
Rated operational voltage U_e	0 / 1000 V
Type of supply voltage	DC

Voltage

Rated operational voltage in DC	900 V
---------------------------------	-------

Electric current

Rated current	3 A
---------------	-----

Fuse

CharactFuse	gPV
Fuse Size	10.3 x 38

Power

Total power loss under I_N	1.2 W
------------------------------	-------

Use conditions

Operating temperature	-25...70 °C
-----------------------	-------------