



LF308PV



PV Fuse-link 10x38 mm 1000V DC 8A

Technical properties

Functions

Release characteristic fuses Super fast (FF)

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1 30 kA

Rated operational voltage U_e 0 / 1000 V

Voltage

Rated operational voltage in DC 1000 V

Electric current

Rated current 8 A

Rated ultimate short-circuit breaking capacity I_{cu} AC IEC 60947-2 30 kA

Frequency

Frequency 50 to 60 Hz

Power

Total power loss under I_N 2.55 W

Standards

European directive WEEE concerned