



LF316G

Cylindrical fuse-links for industrial applications 10x38mm gG 16A 500V AC 120kA

Technical properties

Functions

Release characteristic fuses	Time-lag
------------------------------	----------

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	120 kA
--	--------

Rated operational voltage U_e	500 V
---------------------------------	-------

Type of supply voltage	AC
------------------------	----

Electric current

Rated current	16 A
---------------	------

Rated ultimate short-circuit breaking capacity I_{cu} AC IEC 60947-2	120 kA
--	--------

Fuse

CharactFuse	gG
-------------	----

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under I_N	1.6 W
------------------------------	-------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----