



**PV Fuse-link 10x38 mm 1000V DC 20A**

**Technical properties**

**Functions**

Release characteristic fuses Super fast (FF)

**Main electrical features**

Rated short circuit breaking capacity  $I_{cn}$  AC according IEC60898-1 30 kA

Rated operational voltage  $U_e$  0 / 1000 V

Type of supply voltage DC

**Electric current**

Rated current 20 A

Rated ultimate short-circuit breaking capacity  $I_{cu}$  AC IEC 60947-2 30 kA

**Fuse**

CharactFuse gPV

Fuse Size 10.3 x 38

**Frequency**

Frequency 50 to 60 Hz

**Power**

Total power loss under  $I_N$  2.9 W

LF320PV