



PV Fuse-link 10x38 mm 1000V DC 20A

Technical properties

Functions

Release characteristic fuses	Super fast (FF)
------------------------------	-----------------

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	30 kA
Rated operational voltage U_e	0 / 1000 V

Electric current

Rated current	20 A
Rated ultimate short-circuit breaking capacity I_{cu} AC IEC 60947-2	30 kA

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under I_N	2.9 W
------------------------------	-------

Standards

European directive WEEE	concerned
-------------------------	-----------

LF320PV