



LF325PV

PV Fuse-link 10x38 mm 600V DC 25A

Technical properties

Functions

Release characteristic fuses	Super fast (FF)
------------------------------	-----------------

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	30 kA
Rated operational voltage U_e	0 / 600 V
Type of supply voltage	DC

Electric current

Rated current	25 A
Rated ultimate short-circuit breaking capacity I_{cu} AC IEC 60947-2	30 kA

Fuse

CharactFuse	gPV
Fuse Size	10.3 x 38

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under I_N	2.74 W
------------------------------	--------