



LF332G

**Cylindrical fuse-links for industrial applications 10x38mm gG 32A 400V AC 120kA**

**Technical properties**

**Functions**

Release characteristic fuses	Time-lag
------------------------------	----------

**Main electrical features**

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	120 kA
--	--------

Rated operational voltage $U_e$	400 V
---------------------------------	-------

Type of supply voltage	AC
------------------------	----

**Electric current**

Rated current	32 A
---------------	------

Rated ultimate short-circuit breaking capacity $I_{cu}$ AC IEC 60947-2	120 kA
--	--------

**Fuse**

CharactFuse	gG
-------------	----

Fuse Size	10.3 x 38
-----------	-----------

**Frequency**

Frequency	50 to 60 Hz
-----------	-------------

**Power**

Total power loss under $I_N$	2.9 W
------------------------------	-------

**Safety**

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----