



LF404G

**Industrial fuse-links 14x51 gG 4A**

**Technical properties**

**Functions**

Release characteristic fuses	Fast (F)
------------------------------	----------

**Main electrical features**

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	80 kA
Rated operational voltage $U_e$	690 V
Type of supply voltage	AC

**Electric current**

Rated current	4 A
Rated ultimate short-circuit breaking capacity $I_{cu}$ AC IEC 60947-2	80 kA

**Fuse**

CharactFuse	gG
Fuse Size	14 x 51

**Frequency**

Frequency	50 to 60 Hz
-----------	-------------

**Power**

Total power loss under $I_N$	1 W
------------------------------	-----

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes