



LF408G

Industrial fuse-links 14x51 gG 8A

Technical properties

Functions

Release characteristic fuses Fast (F)

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1 80 kA

Rated operational voltage U_e 690 V

Type of supply voltage AC

Electric current

Rated current 8 A

Rated ultimate short-circuit breaking capacity I_{cu} AC IEC 60947-2 80 kA

Fuse

CharactFuse gG

Fuse Size 14 x 51

Frequency

Frequency 50 to 60 Hz

Power

Total power loss under I_N 1 W

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes