



LF408M

**Industrial fuse-links 14x51 aM 8A**

**Technical properties**

**Functions**

Release characteristic fuses	Time-lag
------------------------------	----------

**Main electrical features**

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	80 kA
Rated operational voltage $U_e$	690 V
Type of supply voltage	AC

**Electric current**

Rated current	8 A
Rated ultimate short-circuit breaking capacity $I_{cu}$ AC IEC 60947-2	80 kA

**Fuse**

CharactFuse	gG ; aM
Fuse Size	14 x 51

**Frequency**

Frequency	50 to 60 Hz
-----------	-------------

**Power**

Total power loss under $I_N$	0.7 W
------------------------------	-------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes