



LF416G

Industrial fuse-links 14x51 gG 16A

Technical properties

Functions

Release characteristic fuses	Fast (F)
------------------------------	----------

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	80 kA
--	-------

Rated operational voltage U_e	690 V
---------------------------------	-------

Type of supply voltage	AC
------------------------	----

Electric current

Rated current	16 A
---------------	------

Rated ultimate short-circuit breaking capacity I_{cu} AC IEC 60947-2	80 kA
--	-------

Fuse

CharactFuse	gG
-------------	----

Fuse Size	14 x 51
-----------	---------

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under I_N	2 W
------------------------------	-----

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----