



LF416G

### Industrial fuse-links 14x51 gG 16A

#### Technical properties

##### Functions

Release characteristic fuses	Fast (F)
------------------------------	----------

##### Main electrical features

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	80 kA
Rated operational voltage $U_e$	690 V
Type of supply voltage	AC

##### Electric current

Rated current	16 A
Rated ultimate short-circuit breaking capacity $I_{cu}$ AC IEC 60947-2	80 kA

##### Fuse

CharactFuse	gG
Fuse Size	14 x 51

##### Frequency

Frequency	50 to 60 Hz
-----------	-------------

##### Power

Total power loss under $I_N$	2 W
------------------------------	-----

##### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes