



LF432M

Industrial fuse-links 14x51 aM 32A

Technical properties

Functions

Release characteristic fuses	Time-lag
------------------------------	----------

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	120 kA
Rated operational voltage U_e	500 V
Type of supply voltage	AC

Electric current

Rated current	32 A
Rated ultimate short-circuit breaking capacity I_{cu} AC IEC 60947-2	120 kA

Fuse

CharactFuse	gG ; aM
Fuse Size	14 x 51

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under I_N	2.04 W
------------------------------	--------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes