



LF540M

Cylindrical fuse-links for industrial applications 22x58mm aM 40A 690V AC 80kA

Technical properties

Functions

Release characteristic fuses	Time-lag
------------------------------	----------

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	80 kA
Rated operational voltage U_e	690 V
Type of supply voltage	AC

Electric current

Rated current	40 A
Rated ultimate short-circuit breaking capacity I_{cu} AC IEC 60947-2	80 kA

Fuse

CharactFuse	aM
Fuse Size	22 x 58

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	3.4 W
---------------------------	-------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes