



LFF2003508014

Trunking 20035,brown

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 20 mm

Length 2000 mm

Trunking width 35 mm

Distance bottom-punch along trunking-direction 125 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 2

Cover, door

Lid shape premounted

Materials

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Internal/useful cross section 440 mm²

Standards

Approvals EN50085-2-1

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK07

Use conditions

Operating temperature -5...60 °C