



LFF2003509010

Trunking 20035,pure white

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	20 mm
Length	2000 mm
Trunking width	35 mm
Distance bottom-punch along trunking-direction	250 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	2
--	---

Cover, door

Lid shape	premounted
-----------	------------

Materials

RAL colour	RAL 9010 - Pure white
Material	PVC
Material group	plastic
Type of surface treatment	untreated
Transparent	No

Cable

Internal/useful cross section	440 mm ²
-------------------------------	---------------------

Equipment

Number of fix dividers	0
Number of plugable separators	0
Cable retainers per meter	0

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP40
REACH conform	Yes
RoHS conform	Yes

Halogen free	No
Impact strength	IK07
Use conditions	
Operating temperature	-5...60 °C
temperatur	
Ambient temperature	-5...65 °C