



LFF2003608014

Trunking 20036,brown

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	20 mm
Length	2000 mm
Trunking width	35 mm
Distance bottom-punch along trunking-direction	125 mm
Distance bottom-punch crosswise trunking-direction	14 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	2
Maximum number of cables (Ø 11 mm, 50% fill)	2

Cover, door

Lid shape	premounted
-----------	------------

Materials

Material group	plastic
Type of surface treatment	untreated
Transparent	No

Cable

Internal/useful cross section	420 mm ²
-------------------------------	---------------------

Equipment

Number of fix dividers	1
------------------------	---

Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature

-5...60 °C