



LFF3004507030

Liféa trunking 30x45 with coupling, grey

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling Pre-equipped with couplers

Dimensions

Trunking height 30 mm

Length 2000 mm

Trunking width 45 mm

Distance bottom-punch along trunking-direction 125 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 5

Cover, door

Lid shape loose

Materials

Colour stone grey

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Internal/useful cross section 970 mm²

Equipment

Cable retainers per meter 2

Standards

European directive RoHS voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature -5...60 °C