



LFF3006009010

Liféa trunking 30x57 with coupling and 2 cable retainer, pure white

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

Dimensions

Trunking height	30 mm
Length	2000 mm
Trunking width	57 mm
Distance bottom-punch along trunking-direction	125 mm
Distance bottom-punch crosswise trunking-direction	18 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	6
--	---

Cover, door

Lid shape	loose
-----------	-------

Materials

RAL colour	RAL 9010 - Pure white
Material	PVC
Material group	plastic
Type of surface treatment	untreated
Transparent	No

Cable

Internal/useful cross section	1250 mm ²
-------------------------------	----------------------

Equipment

Number of fix dividers	0
Number of plugable separators	0
Cable retainers per meter	2

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP40
---------------------	------

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07
Use conditions	
Operating temperature	-5...60 °C
temperatur	
Ambient temperature	-5...65 °C