



LFF4006007030

Liféa trunking 40x57 with coupling and 2 cable retainer, grey

Technical properties

Architecture

Fixing mode	bottom punched
-------------	----------------

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

Dimensions

Trunking height	40 mm
Length	2000 mm
Trunking width	57 mm
Distance bottom-punch along trunking-direction	125 mm
Distance bottom-punch crosswise trunking-direction	18 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	7
--	---

Cover, door

Lid shape	loose
-----------	-------

Materials

Colour	stone grey
RAL colour	RAL 7030 - Stone grey
Material	PVC
Material group	plastic
Type of surface treatment	untreated
Transparent	No

Cable

Internal/useful cross section	1500 mm²
-------------------------------	----------

Equipment

Cable retainers per meter	2
---------------------------	---

Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------