



LFF400637030



Adjustable external corner LF/LFF40060 grey

Technical properties

Architecture

Fixing mode Clipped

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 40 mm

Trunking width 57 mm

Measure a 58 mm

Cover, door

Lid with softlip No

Materials

Colour stone grey

RAL colour RAL 7030 - Stone grey

Material ABS

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 83 / 97 °

Accessories included

Accessory configuration Moulded

Standards

Approvals EN50085-2-1

European directive RoHS voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

