



LFF4009007030

Liféa trunking 40x90 with coupling and 2 cable retainer, grey

Technical properties

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling Pre-equipped with couplers

Dimensions

Trunking height 40 mm

Length 2000 mm

Trunking width 90 mm

Distance bottom-punch along trunking-direction 125 mm

Distance bottom-punch crosswise trunking-direction 40 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 14

Cover, door

Lid shape loose

Materials

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Internal/useful cross section 2650 mm²

Equipment

Number of plugable separators 1

Cable retainers per meter 2

Standards

Approvals EN50085-2-1

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Use conditions

Operating temperature

-5...60 °C