



LFF400957030



## Flat corner LF/LFF40090 grey

### Technical properties

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Dimensions

Trunking height	40 mm
Trunking width	90 mm
Measure a	128 mm

#### Cover, door

Lid with softlip	No
------------------	----

#### Materials

Colour	stone grey
Material	PC-ABS
Type of surface treatment	untreated

#### Installation, mounting

Base punching	Without base punching
---------------	-----------------------

#### Settings

Angle range	90 °
-------------	------

#### Accessories included

Accessory configuration	Moulded
-------------------------	---------

#### Safety

Impact strength	IK07
-----------------	------

#### Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

#### temperatur

Ambient temperature	-5...60 °C
---------------------	------------