



LFF4011007030

**Liféa trunking 40x110 with coupling and 2 cable retainer, grey**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Connectivity**

Trunking coupling Pre-equipped with couplers

**Dimensions**

Trunking height 40 mm

Length 2000 mm

Trunking width 110 mm

Distance bottom-punch along trunking-direction 125 mm

Distance bottom-punch crosswise trunking-direction 60 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 17

**Cover, door**

Lid shape loose

**Materials**

Material group plastic

Type of surface treatment untreated

Transparent No

**Cable**

Internal/useful cross section 3250 mm<sup>2</sup>

**Equipment**

Number of plugable separators 3

Cable retainers per meter 2

**Standards**

Approvals EN50085-2-1

European directive RoHS voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free No

**Use conditions**

---

Operating temperature

-5...60 °C