



LFF401137030



## adjustable external corner LF/LFF40110 grey

### Technical properties

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Connectivity

Trunking coupling	without coupler
-------------------	-----------------

#### Dimensions

Trunking height	40 mm
Trunking width	110 mm
Measure a	68 mm

#### Cover, door

Lid with softlip	No
------------------	----

#### Materials

Colour	stone grey
Material	PC-ABS
Material group	plastic
Type of surface treatment	untreated

#### Installation, mounting

Base punching	Without base punching
---------------	-----------------------

#### Settings

Angle range	83 / 97 °
-------------	-----------

#### Accessories included

Accessory configuration	Moulded
-------------------------	---------

#### Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

#### Use conditions

Operating temperature

-5...60 °C

**temperatur**

---

Ambient temperature

-5...60 °C