



LFF401147030



## adjustable internal corner LF/LFF40110 grey

### Technical properties

#### Architecture

Fixing mode Clipped

#### Configuration

Antibacterial treatment No

#### Connectivity

Trunking coupling without coupler

#### Dimensions

Trunking height 40 mm

Trunking width 110 mm

Measure a 115 mm

#### Cover, door

Lid with softlip No

#### Materials

Colour stone grey

RAL colour RAL 7030 - Stone grey

Material PC-ABS

Material group plastic

Type of surface treatment untreated

#### Installation, mounting

Base punching Without base punching

#### Settings

Angle range 83 / 97 °

#### Accessories included

Accessory configuration Moulded

#### Standards

Approvals EN50085-2-1

European directive RoHs voluntary compliance

#### Safety

Impact strength IK07

#### Use conditions

Operating temperature -5...60 °C

