



LFF401147030



adjustable internal corner LF/LFF40110 grey

Technical properties

Architecture

Fixing mode Clipped

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 40 mm

Trunking width 110 mm

Measure a 115 mm

Cover, door

Lid with softlip No

Materials

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 83 / 97 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

