



LFF401157030



## Flat corner LF/LFF40110 grey

### Technical properties

#### Architecture

Fixing mode Clipped

#### Configuration

Antibacterial treatment No

#### Dimensions

Trunking height 40 mm

Trunking width 110 mm

Measure a 148 mm

#### Cover, door

Lid with softlip No

#### Materials

Type of surface treatment untreated

#### Installation, mounting

Base punching Without base punching

#### Settings

Angle range 90 °

#### Accessories included

Accessory configuration Moulded

#### Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK07

#### Use conditions

Operating temperature -5...60 °C

#### temperatur

Ambient temperature -5...60 °C