



LFF6006007030

## Liféa trunking 60x57 with coupling and 2 cable retainer, grey

### Technical properties

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Connectivity

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

#### Dimensions

Trunking height	60 mm
Length	2000 mm
Trunking width	57 mm
Distance bottom-punch along trunking-direction	125 mm
Distance bottom-punch crosswise trunking-direction	18 mm

#### Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	15
--	----

#### Cover, door

Lid shape	loose
-----------	-------

#### Materials

Colour	stone grey
Material group	plastic
Type of surface treatment	untreated
Transparent	No

#### Cable

Internal/useful cross section	2860 mm <sup>2</sup>
-------------------------------	----------------------

#### Equipment

Cable retainers per meter	2
---------------------------	---

#### Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

#### Safety

Impact strength	IK07
-----------------	------

#### Use conditions

Operating temperature	-5...60 °C
-----------------------	------------