



LFF600647030



## Adjustable internal corner LF/LFF60060 grey

### Technical properties

#### Architecture

Fixing mode Clipped

#### Configuration

Antibacterial treatment No

#### Connectivity

Trunking coupling without coupler

#### Dimensions

Trunking height 60 mm

Trunking width 57 mm

Measure a 135 mm

#### Cover, door

Lid with softlip No

#### Materials

Colour stone grey

Material group plastic

Type of surface treatment untreated

#### Installation, mounting

Base punching Without base punching

#### Settings

Angle range 83 / 97 °

#### Accessories included

Accessory configuration Moulded

#### Standards

European directive RoHS voluntary compliance

#### Safety

Impact strength IK07

#### Use conditions

Operating temperature -5...60 °C

#### temperatur

Ambient temperature -5...60 °C