



LFF600657030



Flat corner LF/LFF60060 grey

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Configuration

Antibacterial treatment	No
-------------------------	----

Dimensions

Trunking height	60 mm
Trunking width	57 mm
Measure a	95 mm

Cover, door

Lid with softlip	No
------------------	----

Materials

Colour	stone grey
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Safety

Protection index IP	IP30
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...60 °C
---------------------	------------