



LFF600947030



adjustable. internal corner LF/LFF60090 grey

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Configuration

Antibacterial treatment	No
-------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	60 mm
Trunking width	90 mm
Measure a	135 mm

Cover, door

Lid with softlip	No
------------------	----

Materials

Colour	stone grey
Material	PC-ABS
Material group	plastic
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	83 / 97 °
-------------	-----------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Impact strength	IK07
-----------------	------

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

