



LFF600957030



Flat corner LF/LFF60090 grey

Technical properties

Architecture

Fixing mode Clipped

Configuration

Antibacterial treatment No

Dimensions

Trunking height 60 mm

Trunking width 90 mm

Measure a 128 mm

Cover, door

Lid with softlip No

Materials

Colour stone grey

Material PC-ABS

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Safety

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

temperatur

Ambient temperature -5...60 °C