



LFF6011007030

**Liféa trunking 60x110 with coupling and 2 cable retainer, grey**

**Technical properties**

**Configuration**

Antibacterial treatment	No
-------------------------	----

**Connectivity**

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

**Dimensions**

Trunking height	60 mm
Length	2000 mm
Trunking width	110 mm
Distance bottom-punch along trunking-direction	125 mm
Distance bottom-punch crosswise trunking-direction	60 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill)	23
--	----

**Cover, door**

Lid shape	loose
-----------	-------

**Materials**

Material group	plastic
Type of surface treatment	untreated
Transparent	No

**Cable**

Internal/useful cross section	5460 mm <sup>2</sup>
-------------------------------	----------------------

**Equipment**

Number of plugable separators	3
Compartment quantity	1
Cable retainers per meter	2

**Standards**

Approvals	EN50085-2-1
European directive RoHS	voluntary compliance

**Safety**

REACH conform	Yes
RoHS conform	Yes

Halogen free	No
Impact strength	IK07
<b>Use conditions</b>	
Operating temperature	-5...60 °C