



LFF601139010



**adjustable external corner LF/LFF60110 pure white**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Configuration**

Antibacterial treatment No

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 60 mm

Trunking width 110 mm

Measure a 48 mm

**Cover, door**

Lid with softlip No

**Materials**

RAL colour RAL 9010 - Pure white

Material PC-ABS

Material group plastic

Type of surface treatment untreated

**Installation, mounting**

Base punching Without base punching

**Settings**

Angle range 83 / 97 °

**Accessories included**

Accessory configuration Moulded

**Standards**

European directive RoHS voluntary compliance

**Safety**

Impact strength IK07

**Use conditions**

Operating temperature -5...90 °C

**temperatur**

