



LFF601149010



adjustable internal corner LF/LFF60110 pure white

Technical properties

Architecture

Fixing mode Clipped

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 60 mm

Trunking width 110 mm

Measure a 135 mm

Cover, door

Lid with softlip No

Materials

RAL colour RAL 9010 - Pure white

Material PC-ABS

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching Without base punching

Settings

Angle range 83 / 97 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHS voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature -5...90 °C

temperatur

