



LFF601159010



Flat corner LF/LFF60110 pure white

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Configuration

Antibacterial treatment	No
-------------------------	----

Dimensions

Trunking height	60 mm
Trunking width	110 mm
Measure a	148 mm

Cover, door

Lid with softlip	No
------------------	----

Materials

RAL colour	RAL 9010 - Pure white
Material	PC-ABS
Type of surface treatment	untreated

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	90 °
-------------	------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	-5...90 °C
-----------------------	------------

temperatur

Ambient temperature	-5...60 °C
---------------------	------------