



LFF601167030



**End cap LF/LFF60110 and LF/LFF40110 grey**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 60 mm

Trunking width 110 mm

**Materials**

Material group plastic

Type of surface treatment untreated

**Standards**

Approvals EN50085-2-1

European directive RoHs voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK07

**Use conditions**

Operating temperature -5...60 °C

**temperatur**

Ambient temperature -5...60 °C