



LFF601167030



## End cap LF/LFF60110 and LF/LFF40110 grey

### Technical properties

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Connectivity

Trunking coupling	without coupler
-------------------	-----------------

#### Dimensions

Trunking height	60 mm
-----------------	-------

Trunking width	110 mm
----------------	--------

#### Materials

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

#### Standards

Approvals	EN50085-2-1
-----------	-------------

European directive RoHS	voluntary compliance
-------------------------	----------------------

#### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Impact strength	IK07
-----------------	------

#### Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

#### temperatur

Ambient temperature	-5...60 °C
---------------------	------------