



LFF6015007030

Trunking 60150, grey with coupler and 2 cable retainer per meter

Technical properties

Connectivity

Trunking coupling Pre-equipped with couplers

Dimensions

Trunking height 60 mm

Trunking width 150 mm

Distance bottom-punch along trunking-direction 125 mm

Distance bottom-punch crosswise trunking-direction 85 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 37

Cover, door

Lid shape loose

Materials

Colour stone grey

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Internal/useful cross section 7122 mm²

Equipment

Number of fix dividers 0

Number of plugable separators 3

Compartment quantity 1 / 4

Cable retainers per meter 2

Standards

European directive RoHS voluntary compliance

temperatur

Ambient temperature -5...65 °C